



HYDROTAP G5 ULTRACARE BCU40 UV NON-CARBON FILTER TOUCH-FREE WAVE TAP CHROME



BOILING



CHILLED

FILTERED

Order Code H5W7U1Z00AUC

Zip HydroTap UltraCare Boiling, Chilled Filtered water system features antimicrobial protection impregnated into key water paths for enhanced hygiene, LED UV-C disinfection, 0.2 micron carbon free internal filtration, Life cycle maintenance plan in a single under bench command centre including full colour interactive touch screen display with pin code protection and customisable settings including boiling water safety mode, 2 energy saving modes including ON/OFF timers and 2 hour sleep mode, 'Quiet' mode with automated intelligent fan speed adjustment, and 100% water efficient air cooled technology. Easy to install integrated ventilation tray included.



Manufacturing Code	H5W7U1Z00AUC
Capacity	Commercial
Boiling Cups per hour	160
Chilled Cups per hour	125

Tap	Zip HydroTap Touch-Free Wave Tap (Chrome)
Water Pressure	Min 170kPa - Max 700kPa
Water Connection	1/2" BSP (G1/2)
Water Supply Requirements	Cold

Water Valves	Integrated 500kPa Pressure limiting valve and Dual Check Valve
Power Rating	1.97kW 220-240V 50Hz
Power Supply	2 x 10 Amp socket outlet
Dimensions	W395mm x D464mm x H333mm
Product Approvals	WaterMark, RCM, ARC
Warranty	5 years (appliance warranty 36 months plus additional 24 months tank warranty)

Installation Requirements

1. Installation and connection of your Zip HydroTap must be carried out by a qualified person, observing national and local regulations.
2. You will require suitable mains electrical and drinking water connections, plus waste water drainage all within 1 metre of the product.
3. Zip Micro is air-cooled so discrete cabinetry cut-outs are required for ventilation.
4. Installation on most bench tops is straightforward however some stone bench tops may require a specialised cutting service.
5. If you live in a hard water area, we recommend installation of a Zip scale filtration kit.
6. Installation by Zip Professional Service can be arranged with a phone call or through www.zipwater.com/book-service-visit

Installation Detail

Ventilation requirements Contact your local service provider if ventilation is not suitable

Clearance envelope
Position the Tap and the Command Centre as close together as possible.

Vent tray (kit no. 93540)

HydroTap Tap options

Classic Plus, Classic, Classic Accessible, Touch-Free Wave

Font options

Raised Font with 135mm Extension, p/n 95258

Mixer Tap options (BCU40 H)

Classic Mixer Tap, **Accessible Mixer Tap**

Detail A. Air inlet grille
Cut-out in cabinet floor

Detail B. Vent Tray air outlet
Cut-out in cabinet floor

Tap Positioning
Position the Tap to dispense into the sink, allowing clearance for a cup or teapot. Alternatively, mount the HydroTap Tap on a Font (available as an accessory).

35mm hole for HydroTap Tap, 35mm hole for Mixer Tap


Vented mixer tap installation
Only cold water supply required

Font with 135mm Extension, p/n 90915

Touch-Free Wave Tap, **Classic Accessible Mixer Tap** (option for vented H models)

Clearance Envelope

RestrictaFlow valve Tee piece



Mains cold water
isolation valve
(not supplied)



BOU40, BOU40 H UltraCare

shown with Touch-Free Wave Tap
and Classic Accessible Mixer Tap (V)

SCALE 1:5
ALL DIMENSIONS IN MM UNLESS OTHERWISE SPECIFIED. INSTALLATION DIAGRAMS ARE FOR ILLUSTRATIVE PURPOSES ONLY. HOSES ARE NOT SHOWN TO SCALE AND CANNOT BE LENGTHENED.